



Philips  
Clock Radio

**FM, Digital tuning**  
Dual alarm



TAR3205

## Wake up ready to go

Keep it simple with this FM digital clock radio. Plenty of presets make station navigation a breeze and you can set the alarm to wake you to a gently rising radio volume. Want to sleep in? Just reach out and hit the snooze button.

### **Compact form. Versatile function**

- FM digital radio
- Digital tuning with up to 10 presets
- Compact build. Dimensions: 131 x 54 x 131 mm

### **Sleep well. Wake gently**

- Gentle Wake. Radio volume slowly increases
- Dual alarm. One clock, two wake-up calls
- Repeat alarm for extra snooze time
- Sleep Timer. Drift off listening to the radio

### **Beautifully simple**

- Clear, simple display
- Key controls on the top panel
- Battery backup if the power fails

**PHILIPS**

# Specifications

## Tuner/Reception/Transmission

- Antenna: FM antenna
- Tuner bands: FM
- FM frequency range: 87.5 - 108 MHz
- No. of preset stations: 10
- RDS: No

## Sound

- Output power (RMS): 200 mW
- Sound System: Mono

## Loudspeakers

- Number of full-range drivers: 1
- Full-range driver diameter: 2"

## Connectivity

- Audio in: No
- Bluetooth: No

## Clock

- Display: LED
- Type: Digital

## Alarm

- No. of alarms: 2
- Alarm source: Buzzer, FM radio
- Snooze (repeat alarm): Yes, 9 mins
- Sleep timer: 15/ 30/ 60/ 90/ 120 mins

## Power

- Power type: AC Input
- AC power input: 100-240 V, 50/60 Hz
- Operation power consumption: <3 W
- Standby power consumption: <1 W
- Backup battery: AAA x 2 (not included)

## Accessories

- Included accessories: Warranty certificate, Quick start guide

## Product dimensions

- Product dimensions (W x H x D):  
13.1 x 5.4 x 13.1 cm
- Weight: 0.204 kg

## Packaging dimensions

- EAN: 48 95229 11120 2
- Packaging dimensions (W x H x D):  
13.6 x 19 x 6 cm
- Gross weight: 0.323 kg
- Net weight: 0.204 kg
- Tare weight: 0.119 kg
- Number of products included: 1
- Packaging type: Box
- Type of shelf placement: Laying

# Highlights

## FM digital radio

The FM tuner delivers clear reception and you can set up to 10 presets for your favourite stations. The display shows the time clearly.

## Sleep Timer

Drift into restful sleep with your favourite station playing in the background. You can set the clock's Sleep Timer to play the radio for up to 2 hours. After your preset time has elapsed, the radio turns off.

## Dual alarm

The dual alarm function lets you set two different alarms and the Gentle Wake function deploys a gradually increasing radio volume to ease you into the day.

## Battery backup

This alarm clock has a battery backup. If there's a power failure, you won't have to reset the clock and your alarm settings will be saved.

