



Philips
Clock Radio

DAB+



TAR5005

Versatile home radio

This small DAB+/FM radio looks great wherever you put it. The wooden cabinet and fabric speaker cover add a dash of minimalist warmth to any room. You get crystal-clear reception, plus a Gentle Wake alarm function that's perfect for guests.

At home with you

- Beautiful design that fits right in
- Wooden cabinet with fabric speaker cover
- Clear, simple black-gloss display
- DAB+/FM radio. Digital tuning with up to 20 presets

Easy listening

- Perfect in any room
- Alarm functions for overnight guests
- Dual alarm. Gentle Wake radio alarm.
- 2.5" full-range speaker driver

Compact and convenient

- Buttons on the top for source, tuning, presets and more
- Dimensions: 95 x 154.5 x 109 mm
- Weight 0.52 kg

PHILIPS

Specifications

Sound

- Output power (RMS): 1 W
- Volume control: up/down

Tuner/Reception/Transmission

- Auto digital tuning
- Station presets: 20
- DAB: info display, menu, smart scan
- Tuner bands: FM, DAB/DAB+

Convenience

- Alarms: Buzzer Alarm, DAB, FM
- Backlight colour: white
- Display type: LCD display

Accessories

- Quick start guide
- Cables/Connection: AC-DC adapter

Power

- Power supply: 100-240 VAC, 50/60 Hz

Alarm

- No. of alarms: 2
- Sleep timer: 15/ 30/ 60/ 90/ 120 mins
- Snooze (repeat alarm): Yes, 9 mins

Dimensions

- Product dimensions (W x H x D):
95 x 154.5 x 109 mm
- Product weight: 0.52 kg
- Packaging dimensions (W x H x D):
236 x 150 x 140 mm
- Weight incl. Packaging: 0.88 kg

Highlights

Perfect in any room

From morning grooves to late-night sounds, this radio fits perfectly on small tables, slim countertops or a bookshelf. The DAB+ tuner delivers crystal-clear reception. You can set up to 20 presets for your favourite stations.

Beautiful design that fits in

A light wood cabinet surrounds the speaker, which is covered in grey speaker fabric. The black gloss display panel shows station information and the time. There are buttons on top of the radio for tuning, source selection and more.

Alarm for overnight guests

Set the Gentle Wake function and your guests will wake to a gradually increasing radio volume. You can use the dual-alarm function to set two different alarms. Perfect if your guests are likely to snooze through the first alarm.

