

Philips  
Original radio

Bluetooth®  
20 W Output Power

TAVS700



## Iconic vibes

Authentic 1950s style meets modern performance in this mains-powered Bluetooth radio. The wooden cabinet, copper dials and dimmable display make this the perfect centerpiece in any room. A digital radio tuner delivers clear reception.

### Iconic looks. Modern performance.

- Vintage wooden cabinet. Period 1950s details
- Clear, detailed sound. 2x3" full-range speakers
- Bass-reflex port. Full, powerful low tones
- Large, clear digital clock display. Dimmable

### Tuned for today

- DAB+ and FM digital radio with presets
- Twin dual-layered control knobs
- 20 W output power
- Copper-toned mesh grille lets the sound flow

### Play it again

- AC-in. Mains-powered
- Up to 10 m wireless range
- Dimensions: 335x146x183 mm
- Weight 2.55 kg

# PHILIPS

# Specifications

## Accessories

- Included accessories: Quick install guide, AC power cord (VDE & UK)

## Loudspeakers

- Built-in speakers: 2

## Sound

- Volume Control: rotary
- Sound system: stereo
- Output power (RMS): 20W

## Compatibility

- other Bluetooth-enabled device

## Connectivity

- Bluetooth profiles: A2DP, AVRCP, HFP
- Bluetooth version: 5
- USB charging: Yes, 5V, 2A
- Bluetooth range: Line of sight, 10M or 30FT

## Tuner/Reception/Transmission

- Auto digital tuning

- Tuner Bands: FM Stereo
- DAB: info display, menu, smart scan
- Tuner bands: DAB (Band III)
- No. of preset stations: 20 (DAB), 20 (FM)
- DAB frequency range: 174.9 - 239.2 MHz
- FM frequency range: 87.5 - 108 MHz
- Tuner Display: PLL

## Convenience

- Clock/Version: Digital
- Clock: sleep timer

## Clock

- Time format: 12H, 24H

## Dimensions

- Product weight: 2.55 kg
- Product dimensions (WxDxH): 33.5 x 14.6 x 18.3 cm
- Weight incl. Packaging: 2.75 kg
- Packaging dimensions (WxDxH): 40.8 x 18.6 x 23.4 cm

# Highlights

## Original radio

This Bluetooth radio pays homage to the iconic Philips Philetta 254 tabletop radio. The vintage wooden cabinet oozes charm. The 1950s detailing on the twin control knobs and speaker grille takes you back to the era when jazz and rock and roll ruled the airwaves.

## Sharp digits. Night and day.

The large, clear digital clock display is dimmable, so it's easy to find the perfect level for your room. When the sun goes down, press the menu knob to access and change the intensity of the illumination.

## Tuned for today

This retro radio features a digital FM tuner for radio—and a Bluetooth connection for streaming from your mobile device. The digital radio tuner delivers crystal-clear reception. You can set up to 20 FM presets and 20 DAB presets for your favourite stations.

## Crisp sound and punchy bass

Two 3" full-range speakers deliver clear sound. A bass-reflex port fills in the low tones, giving you rounded, powerful bass response. The copper-toned mesh grille lets the sound flow.

## Easy pairing. Easy listening.

A short press of the power button gets this radio ready to pair. The wireless range is 10 m: perfect if your device is in another room. Two retro-styled knobs with dual layers offer control of volume, source, DAB+/FM stations, and more.

