

The PHILIPS Kala 6120

With its large numeric and icon display, using PHILIPS Kala 6120 is simplicity in itself. Advantages such as a last number redial, a SOS key and 10 memory speed dials, make this elegantly designed DECT / GAP digital cordless telephone extremely convenient to use. In addition to its outstanding talk and standby times, PHILIPS Kala 6120 benefits from excellent audio quality.

PHILIPS Kala 6822 extra handset**The PHILIPS Kala 6120 main features**

- GAP & PABX Compatible
- 12 hours talk time*
- Over 8 days (200 hours) standby time*
- Up to 50 m maximum indoor range**
- Up to 300 m maximum outdoor range
- LCD 2-line x 10 digits + 1 line of icons
- Length of call indication
- 10 speed dial memories
- SOS key
- Last number redial
- Direct call transfer between handsets
- Free handset-to-handset calls
- Musical Mute / hold
- Adjustable earpiece volume (while in communication)
- Adjustable handset ringer volume
- Three handset ringing melodies
- Easy-to-program
- No external antennae on base or handset
- Light, slimline ergonomic handset: 150 g / 195 cc
- Stand-up handset
- Automatic dialling pause
- Up to 4 handsets for 1 base station
- Up to 2 bases for 1 handset
- Pulse or tone dialling (country dependent)
- Flash Recall
- Standard batteries: 2 AA/LR6 NiCd

Philips Electronique Grand Public

PHILIPS CONFIDENTIAL & PROPRIETARY



Technical specifications

Power Supply

Handset : 2 x AA/LR6 1.2 V 600 mAh NiCd

Base : 8V AC / 250 mA

Compliance

ETS 300-329

EN 60950

CTR 6

CTR 10

CTR 22

Performance

12 hours talk*
8 days (200 hours) standby*

Dimensions

Base: 121 x 120 x 85

Handset: 53 x 163 x 35

Package (TD 6120): 200 x 174 x 105

Package (TD 6822): 174 x 164 x 65

LED indicators

Base : Line/Power

Weight

Base : 199 g

Handset : 150g

Warning indicators

Handset : Battery discharged

Handset Keys

Dialling keypad
Memories
SOS
Redial
Line
Internal call
Recall / Menu
Earpiece volume control

Temperature range

Operation : 0°C to + 40°C

Storage : -25°C to + 70°C

Relative humidity

Operation : Up to 95 % at 40°C

Storage : Up to 95 % at 40°C

Cabinet finishing

Non-gloss

Package contents

Handset
Base
2 extra base station colour clips
2 AA/R6 NiCd batteries
Telecom line cord
Power adapter
User manual

Icons

Battery
Programming
Memories
Line
Internal call / Musical mute
Range

Radio RF power < 250 mW

Range

Indoor : up to 50m max indoor range**

Outdoor : up to 300m max outdoor range**

* Quoted talk and standby times with 2 AA/LR6 600 mAh NiCd batteries

** The quoted range is under ideal conditions, i.e. with no obstacles between the base and handset.

The range of DECT cordless telephones depends on:

- the environment in which the base station is located: thick walls, metallic window frames etc. near the base will reduce the phone's range
- the presence of obstacles between the base station and handset: for example, when using a handset in the garden with the base station inside the house, the range may be reduced by the exterior wall of the house.

Availability in individual countries depends on approval by the relevant authorities. Data subject to alteration without notice.

Let's make things better.