

Dect Digital Cordless telephone

# *Direct Phonebooks with Icons*

- Original, unobtrusive design
- Innovative scrolling alphanumeric LCD
- Icon menu management system
- 2 phonebooks with specific icons & melodies
- CLI with direct call log key



*Let's make things better.*



**PHILIPS**

# Additional Features & Benefits

KALA 200 / TD 6131

## Main Features

- Alphanumeric LCD : 1-line x 10 digits + 3 lines of icons
- 2 phonebooks of 10 entries each
- 12 hours talk time
- Over 8 days standby time
- Caller identification / call waiting
- Call log of last 10 numbers received
- Direct call log key
- Direct earpiece volume control
- 7 handset ringing melodies
- 5 Last number redials
- Easy-to-program via icon menu management
- Direct call transfer between handsets
- Free handset-to-handset calls
- Musical Mute / hold
- Paging key
- Fast antennae selection technology (FAST)
- Adjustable handset ringer volume
- No external antennae on base or handset
- Light, slimline ergonomic handset: Reversible & stand-up handset
- Up to 4 handsets for 1 base station Flash Recall
- Standard batteries: 2 AA/LR6 NiCd
- Clear key
- GAP & PABX Compatible
- Up to 50 m maximum indoor range<sup>1</sup>
- Up to 350 m maximum outdoor range<sup>1</sup>

Philips France - S.A.S. au capital de 111 000 000 Euro - Siège social: 2 rue Benoit Malon, 92156 Suresnes Cedex - RCS Nanterre B 402 805 527 All rights reserved. Reproduction in whole or in part is expressly prohibited without the prior written consent of the copyright owner. Philips reserves the right to modify the specifications mentioned in this document at any time and without prior notice.

© 2000 Philips Consumer Communications  
Division of Philips France  
Printed in France

## Technical specifications

### Power Supply

Handset : 2 x AA/LR6 1.2V 600 mAh NiCd  
Base : 8V DC / 250 mA Output 1  
6.5V AC / 95 mA Output 2

### Performance

- 12 hours talk
- 8 days (200 hours) standby

### Handset Keys

- Line ➤ Dialling keypad ➤ 2 phonebooks key (friends & family) ➤ Internal call / Ok key ➤ Redial / clear key
- Call log ➤ Recall / Menu ➤ Earpiece volume control
- Base station key

### Base key

- Paging

### Menu Icons

- Musical note (for ringing melodies)
- Additional handset (for subscription)
- Spanner (for settings)

### Hard Icons

- Battery ➤ Call log ➤ Phonebook 1 : friend
- Phonebook 2 : family ➤ Line ➤ Internal call
- Message ➤ Antennae

### Norms

- TBR 6 (radio)
- EN 60950(92) (security)
- ETS 300329 (97) (security)

### Dimensions

Base : 130x165x50  
Handset : 152mm  
Package ( Kala 200 Basic) : 185x125x138  
Package ( Kala 200 extra handset) : 185x140x67

### Weight

Base : 171g  
Handset : 155g

### Temperature range

Operation : 0°C to + 40°C  
Storage : -25°C to + 70°C

### Relative humidity

Operation : Up to 95 % at 40°C  
Storage : Up to 95 % at 40°C

### Package contents

- Handset ➤ Base ➤ 2 AA/R6 NiCd batteries
- Telecom line cord ➤ Power adapter ➤ User manual

Radio RF power < 250 mW

### Philips Compliance

- CTR 37 ➤ TBR 10 (acoustic) ➤ TBR 22

1 - The quoted range is under ideal conditions, i.e. with no obstacles between the base and handset.  
The range of DECT cordless telephones depends on:  
• the environment in which the base station is located: thick walls, metallic window frames etc. near the base will reduce the phone's range  
• the presence of obstacles between the base station and handset: for example, when using a handset in the garden with the base station inside the house, the range may be reduced by the exterior wall of the house.

Availability in individual countries depends on approval by the relevant authorities. Data subject to alteration without notice.

Let's make things better.



PHILIPS