

# Additional Features & Benefits

zenia  
6326

## Handset Features

- > LCD + keypad backlight
- > GAP / PABX compliant
- > Standard batteries : 2 AAA NiMH
- > 16 hours talk time<sup>1</sup>
- > 10 days standby time<sup>1</sup>
- > 50 m maximum indoor range<sup>2</sup>
- > 300 m maximum outdoor range<sup>2</sup>
- > Crystal Sound System (CS<sup>3</sup>)
- > Fast antenna selection technology
- > Graphic LCD 4 lines of 14 characters + 1 line of icons
- > Full duplex CS<sup>2</sup> hands-free system (base)
- > Mobile handset hands-free
- > 10 Last number redial stack
- > Belt clip
- > Headset plug
- > 7 Direct dialling keys (base)
- > Musical Mute / hold
- > Base-handset intercom
- > Baby-sit function
- > 6 ringing melodies
- > Light, slimline ergonomic handset: 110 g / 125 cc
- > Stand-up handset
- > Automatic dialling pause
- > Up to 6 handsets for 1 base station
- > Up to 4 bases for 1 handset
- Pulse or tone dialling (country dependent)**
- > Menu driven with graphic display & soft key
- > 200 name + number phone book

- > CLI / CW with call log list of 30 entries
- > CLI name display
- > Paging function / Family link key
- > Stand alone wall mounted or desktop base station

- 1 - Quoted talk and standby times with 2 AAA 600 mAh NiMH batteries
- 2 - The quoted range is under ideal conditions, i.e. with no obstacles between the base and handset. The range of DECT cordless telephones depends on:
  - the environment in which the base station is located : thick walls, metallic window frames etc. near the base will reduce the phone's range
  - the presence of obstacles between the base station and handset: for example, when using a handset in the garden with the base station inside the house, the range may be reduced by the exterior wall of the house.

## Technical specifications

### Power Supply

Handset : 2xAAA 1.2 V 600 mAh NiMH  
Base : 9V DC / 600 mA  
Handset charger : 8V DC / 250 mA

### LED indicators

Base : Line / Power  
Warning indicators  
Handset : Battery discharged

### Handset Keys

> Line > Soft Key > Arrow up and down  
> Cancel / Recall > Dialling keypad  
> Loudspeaker > Volume boost

### Icons

> Battery level > Voice mail enable  
> New mail > Silence > Loudspeaker  
> Line / Internal call / musical mute  
> In range / Out of range / Not locked

**Radio RF power** : < 250 mW

### Compliance

> ETS 300-329 > EN 60950 > CTR 6  
> CTR 10 > CTR 22

### Dimensions

Base station : 143 x 126 x 45  
Handset : 130 x 47 x 23  
Charger : 90 x 77 x 70  
Package : 292 x 143 x 121

### Weight

Base : 250g  
Handset : 110g

### Temperature range

Operation : 0°C to + 40°C  
Storage : -25°C to + 70°C

### Relative humidity

Operation : Up to 95 % at 40°C  
Storage : Up to 95 % at 40°C

**Cabinet finishing** : Non-gloss

### Package contents

> Handset > Base Station  
> Handset charger > Belt clip  
> 2 AAA NiMH batteries > Telecom line cord  
> 2 Power adapters > User manual

2000 Philips France. All rights reserved.  
The information and specifications included are subject to change without prior notice. Philips tries to ensure that all information in this document is correct, but does not accept liability for any error or omission.

© 2000 Philips Consumer Communications  
Division of Philips France  
Printed in France  
4311 256 00851

Let's make things better.



PHILIPS