

Digital Cordless telephone

Handsfree on handset

- > Icon melody caller identification with unique, harmonious guitar sounds
- > Easy access to Operator Services
- > Prefix management / least cost routing
- > *es⁺* - *CRYSTAL SOUND SYSTEM*
- > Ease of use - 2 soft keys & scrolling menus



Let's make things better.



PHILIPS

Main Features

- > **Graphic LCD** 3 lines of 16 characters + 1 line of icons
- > **Menu driven** with graphic display & 2 soft keys
- > **150 name & number** phonebook
- > **CLI / CW** with call log list of 40 entries
- > **Icon melody** caller identification
- > **CLI name display**
- > **Handsfree** on handset
- > **5 ringing melodies & 4 unique** guitar melodies
- > **Prefix management / least cost** routing
- > **Easy access** to operator services
- > **Crystal Sound System (CS²)**
- > **Fast Antenna Selection Technology (F.A.S.T.)**
- > **5 Last number** redial stack
- > **Belt clip**
- > **Musical Mute / hold**
- > **Baby-sit function** (with extra handset)
- > **Paging function**
- > **Stand-up handset**
- > **Wall mounted** or desktop base station
- > **Date and time** dynamic back up
- > **Date / time synchronization** with caller identification
- > **Light, slimline ergonomic handset :** 120 g / 140 cc
- > **Up to 8 handsets** for 1 base station
- > **Up to 4 bases** for 1 handset
- > **Pulse or tone dialling** (country dependent)
- > **GAP compliant**
- > **Standard batteries : 2 AAA NiMH**

Technical specifications

Power Supply

Handset : 2 x AAA 1.2V 550 mAh NiMH
Base : Input 1 : 8V DC / 250 mA
Input 2 : 6.5V AC / 95 mA

Performance

- > 15 hours talk ¹
- > 10 days standby ¹

LED indicators

Base : Line / power

Handset Keys

- > Line > 2 Soft Keys > Up / down navigation keys
- > Cancel / Recall > Dialling keypad > Loudspeaker
- > Volume key > Least cost routing / prefix key
- > Intercom / Family Link key

Icons

- > Battery level > New mail > Line / Internal call
- > Silence > Loudspeaker > In range / Out of range
- > Identity withheld

Radio RF power : < 250 mW

Range

Indoor : 50 m max indoor range ²
Outdoor : 300 m max outdoor range ²

Compliance

- > ETS 300-329 > EN 60950 > CTR 6 > CTR 10
- > CTR 22

Dimensions

Base : 150 x 123 x 81
Handset : 50 x 28 x 153
Charger : 77 x 76 x 92

Weight

Base : 230 g
Handset : 120 g

Temperature range

Operation : 0°C to + 40°C
Storage : -25°C to + 70°C

Relative humidity

Operation : Up to 95 % at 40°C
Storage : Up to 95 % at 40°C

Cabinet finishing : Non-gloss

Package contents

- > Handset > Base Station > Belt clip > 2 AAA NiMH batteries > Telecom line cord > Power adapter > User manual

1 - Quoted talk and standby times with 2 AAA 600 mAh NiMH batteries

2 - The quoted range is under ideal conditions, i.e. with no obstacles between the base and handset.

The range of DECT cordless telephones depend on :

- the environment in which the base station is located : thick walls, metallic window frames ect. near the base will reduce the phone's range
- the presence of obstacles between the base station and handset : for example, when using a handset in the garden with the base station inside the house, the range may be reduced by the exterior wall of the house.