

The PHILIPS Kala 6523

Equipped with a quality digital answerphone, outstanding talk and standby times, base station loudspeaker, PHILIPS 6523 is an extremely easy to use DECT / GAP digital cordless phone. Its elegant, ergonomic design is enhanced by many benefits such as the large numeric display with icons, 10 memory speed dials, last number redial and adjustable audio volumes.

PHILIPS Kala 6822 extra handset**The PHILIPS Kala 6523 main features**

- GAP & PABX Compatible
- 12 hours talk time*
- Over 8 days (200 hours) standby time*
- Up to 50 m maximum indoor range**
- Up to 300 m maximum outdoor range**
- High / Standard quality digital answerphone
- Remote and direct access to the answerphone
- Answer only / record mode
- Call filtering
- LCD 2-line x 10 digits + 1 line of icons
- Loudspeaker on base station
- 10 speed dial memories
- Last number redial
- Direct call transfer between handsets
- Free handset-to-handset calls
- Musical Mute / hold
- Adjustable handset ringer volume
- Adjustable earpiece volume
- Adjustable loudspeaker volume
- Adjustable base ringer volume (+ silent)
- Three handset ringing melodies
- Easy-to-program
- No external antennae on base or handset
- Light, slimline ergonomic handset: 150 g / 195 cc
- Stand-up handset
- Automatic dialling pause
- Up to 4 handsets for 1 base station
- Up to 2 bases for 1 handset
- Pulse or tone dialling (country dependent)
- Flash Recall
- Standard batteries: 2 AA/LR6 NiCd

Technical specifications

Power Supply

Handset : 2 x AA/LR6 1.2 V 600 mAh NiCd
 Base : 8V AC / 250 mA

Range

Indoor : up to 50m max indoor range**
 Outdoor : up to 300m max outdoor range**

Compliance

ETS 300-329
 EN 60950
 CTR 6
 CTR 10
 CTR 22

Performance 12 hours talk*
 8 days (200 hours) standby*

LED indicators

Base : Line/Power

Dimensions

Base: 121 x 120 x 85
 Handset: 53 x 163 x 35
 Package (TD 6523): 200 x 174 x 105
 Package (TD 6822): 174 x 164 x 65

Warning indicators

Handset : Battery discharged

Weight

Base : 199g
 Handset : 150g

Handset Keys

Dialling keypad
 Memories
 Answering machine
 Redial
 Line
 Internal call
 Recall / Menu
 Loudspeaker

Temperature range

Operation : 0°C to + 40°C
 Storage : -25°C to + 70°C

Icons

Battery
 Programming
 Memories
 Line
 Internal call / musical mute
 Range
 Message
 Loudspeaker

Relative humidity

Operation : Up to 95 % at 40°C
 Storage : Up to 95 % at 40°C

Cabinet finishing

Non-gloss

Package contents

Handset
 Base
 2 extra base station colour clips
 2 AA/R6 NiCd batteries
 Telecom line cord
 Power adapter
 User manual

Radio RF power < 250 mW

* Quoted talk and standby times with 2 AA/LR6 600 mAh NiCd batteries

** The quoted range is under ideal conditions, i.e. with no obstacles between the base and handset.

The range of DECT cordless telephones depends on:

- the environment in which the base station is located: thick walls, metallic window frames etc. near the base will reduce the phone's range
- the presence of obstacles between the base station and handset: for example, when using a handset in the garden with the base station inside the house, the range may be reduced by the exterior wall of the house.

Availability in individual countries depends on approval by the relevant authorities. Data subject to alteration without notice.

Let's make things better.

