

ONIS Memo 6411



The ONIS Memo is a DECT/GAP digital cordless telephone offering world-beating talk and standby times, exceptional sound quality and range, and innovative features in an elegant, easy-to-use design.

ONIS 6810 extra handset



ONIS Memo 6411 main features

- Listen-in loudspeaker on handset
- Memo answerphone
 - 6 minute capacity
 - High quality audio
 - Date and time stamping
 - Local message recording
 - Answer-only or answer & record
 - All controls from handset
 - Remote control via phone line
- Caller Identification* (CLIP) / Call Waiting* (CW)
- 20-entry CLIP Call Log*
- Baby monitor function (with 2 handsets)
- 14 hours talk time**
- 8+ days (195 hours) standby time**
- 1 month standby time in powersave mode**
- GAP certified
- Standard batteries: 2 AA/R6 NiCd/NiMH*
- No external antenna on base or handset
- Light, slimline ergonomic handset: 160 g / 175 cc
- 10 character scrolling alphanumeric LCD display
- Easy-to-use menus
- 40-name phonebook
- Chain dialling from phonebook
- Stand-up handset and 2-position charging
- Call duration display
- Call cost display*
- Dialling preparation with correction
- Last number redial
- Automatic dialling pause
- PABX compatible
- Pulse or tone dialling*
- Flash Recall*
- Adjustable base and handset ringer volume
- Adjustable earpiece volume
- Up to 4 handsets with one base
- Free handset-to-handset calls
- Call transfer between handsets
- Up to 4 bases for one handset
- Auto base search (off-line)
- Three ringing melodies for handset and base
- Base and handset ringer on/off
- Up to 50 m maximum indoor range***
- Up to 300 m maximum outdoor range***

ONIS 6810 extra handset plus charger

- All Onis 6411 features
- Desk or wall mountable charger

Philips Consumer Communications

A Lucent Technologies and Philips Electronics venture



PHILIPS

Technical specifications

Power Supply

Handset : 2 x AA/LR6 1.2 V 600 mAh NiCd
 2 x AA/LR6 1.2 V 1200 mAh NiMH*
 Base : 9V AC / 220 mA
 Charging current : 11V DC / 60 mA (Onis 6411)
 6V DC / 70 mA (Onis 6810)

Performance

14 hours talk**
 195 hours standby**
 720 hours powersave standby**

LED indicators

Base : Line/Power/Memo

Warning indicators

Handset : Out of range
 Battery discharged

Handset LCD Display

Handset : 10 character alphanumeric
 9 icons

Handset Keys

Hookswitch
 Loudspeaker
 Memo
 Menu Up, Down, OK
 Phonebook
 4 x 3 keypad (0...9, # and *)
 Recall/Menu
 Internal call
 Redial
 Call Log

Radio RF power < 250 mW

Range

Indoor : up to 50m max indoor range***
 Outdoor : up to 300m max outdoor range***

Compliance

ETS 300-329
 EN 60950
 CTR 6
 CTR 10
 CTR 22

Dimensions

Base: 180 mm x 100 mm x 52 mm
 Handset: 165 mm x 60 mm x 30 mm
 Package (Onis 6411): 295 mm x 260 mm x 70 mm
 Package (Onis 6810): 147 mm x 260 mm x 62 mm

Weight

Base : 155 g
 Handset : 160 g

Temperature range

Operation : 0°C to + 40°C
 Storage : -25°C to + 70°C

Relative humidity

Operation : Up to 95 % at 40°C
 Storage : Up to 95 % at 40°C

Cabinet finishing

Non-gloss

Package contents

Onis 6411 : Handset
 Base
 2 AA/LR6 NiCd* batteries
 Telecom line cord
 Power block and cord
 User manual
 Onis 6810 : Handset
 Charger
 2 AA/LR6 NiCd* batteries
 Power block and cord
 User manual

* Country dependent
 ** Quoted talk and standby times with 2 AA/LR6 600 mAh NiCd batteries
 *** The quoted range is under ideal conditions, i.e. with no obstacles between the base and handset.
 The range of DECT cordless telephones depends on:
 - the environment in which the base station is located: thick walls, metallic window frames etc. near the base will reduce the phone's range
 - the presence of obstacles between the base station and handset: for example, when using a handset in the garden with the base station inside the house, the range may be reduced by the exterior wall of the house.

Availability in individual countries depends on approval by the relevant authorities. Data subject to alteration without notice.

Let's make things better.

