

Dect Digital Cordless handset

Additional Handset

- > Handsfree on handset
- > Original, innovative scrolling alphanumeric LCD with Icon menu management system
- > 2 phonebooks with specific icons & melodies
- > CLI with direct call log key



Let's make things better.



PHILIPS

Additional Features & Benefits

KALA 200 / TD 6830 additional handset

Main Features

- Alphanumeric LCD : 1-line x 10 digits + 3 lines of icons
- 2 phonebooks of 10 entries each
- 12 hours talk time
- Over 8 days standby time
- Caller identification / call waiting
- Call log of last 10 numbers received
- Earpiece volume control
- 3 high quality musical & 4 traditional ringing melodies
- 5 Last number redials
- Easy-to-program via icon menu management
- Direct call transfer between handsets
- Free handset-to-handset calls
- Musical Mute / hold
- Fast antennae selection technology (FAST)
- Adjustable handset ringer volume
- No external antennae on base or handset
- Light, slimline ergonomic handset: stand-up handset
- Up to 4 handsets for 1 base station
- Flash Recall
- Standard batteries: 2 AA/LR6 NiCd
- Clear key
- GAP & PABX Compatible
- Up to 50 m maximum indoor range¹
- Up to 350 m maximum outdoor range¹

Technical specifications

Power Supply

Handset : 2 x AA/LR6 1.2V 600 mAh NiCd

Performance

- 12 hours talk
- 8 days (200 hours) standby

Handset Keys

- Line ➤ Dialling keypad ➤ 2 phonebooks key (friends & family) ➤ Internal call / OK key
- Redial / clear key ➤ Call log ➤ Recall / Menu
- earpiece volume control

Handset back housing key

- Answerphone message play key if subscribed to a 6533 base.

Menu Icons

- Cassette (for answerphone) ➤ Musical note (for ringing melodies) ➤ Additional handset ➤ Spanner (for settings) ➤ Earpiece (for earpiece volume)

Hard Icons

- Battery ➤ Call log ➤ Phonebook 1 : friend
- Phonebook 2 : family ➤ Line ➤ Internal call
- Message ➤ Antennae

Norms

TBR 6 (radio)
EN 60950(92) (security)
ETS 300329 (97) (security)

Dimensions

Handset : 152mm
Package (Kala 200 extra handset) : 185x140x67

Weight

Charger : 67g
Handset : 152g

Temperature range

Operation : 0°C to + 40°C
Storage : -25°C to + 70°C

Relative humidity

Operation : Up to 95 % at 40°C
Storage : Up to 95 % at 40°C

Package contents

- Handset ➤ Charger ➤ 2 AA/R6 NiCd batteries
- Power adapter ➤ User manual

Radio RF power

< 250 mW

Philips Compliance

CTR 37
TBR 10 (acoustic)
TBR 22

1 - The quoted range is under ideal conditions, i.e. with no obstacles between the base and handset. The range of DECT cordless telephones depends on:

- the environment in which the base station is located: thick walls, metallic window frames etc. near the base will reduce the phone's range
- the presence of obstacles between the base station and handset: for example, when using a handset in the garden with the base station inside the house, the range may be reduced by the exterior wall of the house.

Availability in individual countries depends on approval by the relevant authorities. Data subject to alteration without notice.

Philips France - S.A.S. au capital de 111 000 000
Euro - Siège social : 2 rue Benoit Malon, 92156
Suresnes Cedex - RCS Nanterre B 402 805 527
All rights reserved. Reproduction in whole or in
part is expressly prohibited without the prior
written consent of the copyright owner.
Philips reserves the right to modify the specifica-
tions mentioned in this document at any time and
without prior notice.

© 2000 Philips Consumer Communications
Division of Philips France
Printed in France

Let's make things better.



PHILIPS