

pronto

Intelligent Remote Control

TS1000

Intelligent Remote Control with LCD Touchscreen Display

- *Unique and fully-customizable learning remote control*
- *Total control of IR-based consumer electronics products*
- *Dynamic display with familiar buttons and simple menus*
- *Intuitive and animated user interface with scrolling-menu options*
- *Easy to program and save commands in non-volatile memory*
- *Design and personalize buttons, panels, and devices with customized labels and icons*
- *Programmable and editable macros*
- *Uniquely stylish and lightweight design for convenience of use*
- *Easy visibility with large LCD screen, backlight, and auto-zoom features*
- *Pre-programmed with RC5 and RC6 codes for Philips and Marantz components*
- *Optional recharging dock with rechargeable NiMH battery pack and AC adapter*



intelligent remote control

Let's make things better.



PHILIPS



Pronto is a universal learning remote control that combines elegance, flexibility, and ease of use. It combines a large touchscreen display with an intuitive user interface and direct-access buttons to conveniently provide home entertainment control.

Customization (Pronto is as unique as you are!)

Remote controls are typically limited to a certain number of components and/or functions—not this one. Pronto's unparalleled design combines the benefits of a dynamic, digital user interface with direct access buttons. It's easy to add, delete, and label new buttons or menus. This allows maximum customization according to individual needs and tastes. A special feature prevents tampering with stored commands. It's easy to personalize Pronto—set up and change the user interface with any number of components. Pronto is as unique as you are.

Total Control (Learning universal and expandable)

Pronto can control almost all infrared (IR) receiving devices. It comes preprogrammed with RC5 and RC6 commands for Philips and Marantz components. It can learn new codes—any brand—and even grow in functionality as your system changes to accommodate new components. Pronto gives you the ability to add buttons, devices, and macro functions as desired. The non-volatile flash memory secures the programming even if the batteries are removed.

Interactive User Interface - (Simplicity and flexibility)

The intuitive graphical user interface is easy to understand. The dynamic display uses familiar icons and sliding menus which allow for quick and easy execution of commands. Pronto allows for maximum flexibility for even the most sophisticated home entertainment systems.

Unique and Elegant Design


The stylish design makes it not only attractive but practical for daily use. The product is designed to accommodate one or two-handed, cradled in the recharging dock, or tabletop operation. Automatic light sensors and backlighting make it convenient to use Pronto in the dark.

Expandable and Upgradeable

Pronto's built in two-way IR input/output, coupled with its two-way RS232 communication serial port ensures that it's a wise investment. These standard external ports guarantee compatibility and make it easy to upgrade with future components and applications.

Pronto Intelligent Remote Control (TS1000)

- Direct-Access Buttons
 - Mute
 - Channel Up/Down
 - Volume Up/Down
 - Right/Left Configuration Buttons
 - Backlight Button
- Light Sensing Photocell
- Send/Learning IR Eyes
- Hardware
 - Built-in IR Codes RC-5, RC-6
 - IR Operating Distance < 33 ft (70 m W/SR, 0 degrees) or < 10 m (70 m W/SR, 0 degrees) or +/- 30 degrees (@16ft or 5 m)
 - IR Operating Angle 1 inch or 2.5cm minimum @ +/- 40 degrees 1ft or 30 cm maximum @ up to 40 degrees
 - IR Learning Distance Up to 56 kHz
 - IR Learning Frequencies Auto power up/down (no on/off switch)
 - Automatic Power Mgmt Four (4) AA 1.5V batteries included
 - Battery Type 6 months typical usage based on 50% battery life after 21 hours of continuous use and active use of back lighting
 - Battery Life 65uA
- Standby Current
- LCD
 - Dynamic LCD Input Finger or capped pen
 - Resolution 320 x 240, 0.24 mm pitch
 - Refresh Rate 70 Hz
 - Color Scales 4 gray levels
 - Dimensions 3 x 2.3 inches or 77 x 58 mm DFSTN
- Memory (unlimited devices & macros within memory)
 - SRAM 512 KB (0.5 MB)
 - Flash 1024 KB (1 MB)
 - Output 1.3Cd/m2
- EL Back-Light Luminance
- Audio: Piezo Speaker Speakers with adjustable volume (4 KHz)
- Processor Motorola DragonBall MC68328
- Ports 3 wire connector (RS232 serial port)
- Weight 8.8 oz or 250 g with batteries
- Dimensions 5.4 x 3.6 x 1.5 inches or 138 x 92 x 38 mm (length x width x height)
- Warranty 1 year warranty
- Package Contents Pronto remote control, instructional manual, warranty and registration cards, and four (4) AA batteries



Pronto Recharge Package (DS1000)

- Optional Accessory - Sold Separately
- Rechargeable Battery Pack 4.8V NiMH, 2.2 x 2.245 x .6 inches, .25 lbs
- Recharge Docking Station with LED Indicator 5.9 x 3.554 x 1.12 inches, .41 lbs
- AC Transformer 110/220V to 12V, 700mA, 3.65 x 2.88 x 2.17 inches, .8 lbs

Specifications subject to change without notice.

©1999 Philips Digital Electronics Group
A Division of Philips Electronics North America Corporation

UPC Codes: TS1000 - 037849876664 and DS1000 - 037849876671

KID Design #99265 Printed in the USA

More information, web site: www.mmhometheater.com or www.pronto.philips.com

Let's make things better.



PHILIPS