

Philips
HDMI cable

12 ft

High speed

US2-P72810



Supports resolutions up to 1080p

with this High Speed HDMI™ cable

New High Speed HDMI™ delivers the best digital audio and video performance possible with resolutions up to 1080p.

HDMI™ version 1.3a

- Deep Color™
- Lossless Audio™

Enjoy better picture/sound quality

- High purity copper conductor for reliable signal transfer
- 24 carat gold-plated connectors optimize signal

Protects against signal loss

- Copper braided reinforced aluminum shielding

Easy installation

- Plug and play for easy use

Enjoy extended durability

- Protective metal shell for extended durability
- Flexible PVC jacket
- Rubber strain relief

PHILIPS

sense and simplicity

HDMI cable
12 ft High speed

Specifications

Packaging dimensions

- **Packaging dimensions (W x H x D):**
7.75 x 11 x 1.75 inch
- **Nett weight:** .31114 lb
- **Gross weight:** .37263 lb
- **Tare weight:** .06148 lb

Outer Carton

- **Gross weight:** 4.2 lb
- **Outer carton (L x W x H):** 10 x 7.2 x 12.5 inch
- **Nett weight:** 1.24456 lb
- **Tare weight:** 2.95544 lb

US2-P72810

Product highlights

Deep Color™

Supports 30-bit, 36-bit and 48-bit (RGB or YCbCr) color depths, allowing HDTVs to go from millions of colors to billions of colors. Enables increased contrast ratio. Eliminates on-screen color banding for smooth tonal transitions and subtle gradations between colors.

Lossless Audio™

Supports new lossless compressed digital audio formats Dolby TrueHD and DTS-HD.

Braided shielding

Copper braided reinforced aluminum shielding protects against signal loss and interference.

Plug and play

Plug and play offers easy installation of components without time-consuming installations.

Metal shell

The metal shell protects the internal connection of the cable. It ensures durability and the reliability of your connection.

High purity copper

This copper conductor provides high accuracy in signal transfer with minimal resistance.

24 carat gold-plated connector

24 carat gold-plated connectors ensure the best signal quality for your components.

Flexible PVC Jacket

Flexible PVC jacket provided protection to the delicate core of the cable. It also offers extended durability and ease of installation.

Rubber strain relief

Rubber strain relief provides a secure, yet flexible juncture between the cable and the plug.



Issue date 2008-12-10

Version: 1.0.6

12 NC: 8670 000 45267
UPC: 0 26616 02035 5

© 2008 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com