


Philips
VCR with Turbo Drive

NICAM

VR750



A HiFi video recorder to match your lifestyle

A class act

Best Picture

- Digital Studio Picture Control optimises playback picture
- Smart Picture provides personalised image settings
- Plays tapes recorded in NTSC on your PAL TV

Great convenience

- Turbo Drive means speed, reliability and intelligence
- Follow TV copies the TV's channel order
- VPS/PDC records the program exactly when it starts
- Automatically selects long play if insufficient tape is left
- Front A/V Connectors mean no crawling behind the set

Record your favourite programmes

- VIDEO uses a single code to program the timer
- Turbo Timer is the fastest way to program a recording timer
- Record Link enables recording from external sources

Best sound

PHILIPS

Technical specifications

Video Recording

- **Recording system:** PAL
- **Tape speeds:** LP, SP
- **Tape speed selection:** Automatic long play recording

Video playback

- **Number of video heads:** 4
- **Playback enhancement:** Digital Studio Picture Control, Studio Tracking System, Video Index Search System
- **Rewinding time E-180:** 70 s
- **Video enhancement:** Smart Picture
- **Video tape playback system:** NTSC, PAL
- **Videotape enhancements:** Tape Length Recognition, Turbo drive deck
- **Head cleaner:** Auto

Tuner / Reception / Transmission

- **Number of preset channels:** 099
- **Tuner bands:** Hyper band, S channel, UHF, VHF
- **TV system:** PAL I

Sound

- **Sound system:** Mono, Nicam stereo, Stereo

Audio Playback

- **Number of audio heads:** 1 linear, 2 rotative

Connectivity

- **Ext 1 Scart:** Audio L/R, CVBS in/out

- **Ext 2 Scart:** Audio L/R, CVBS in/out
- **Front:** Audio L/R in, CVBS in
- **Output rear:** Audio L/R out

Convenience

- **Clock:** Smart clock
- **Ease of installation:** Analogue Follow TV, Autoinstall
- **OSD languages:** English
- **Programmable events:** 8
- **Programming period:** 12 month
- **Programming/Timer Enhancements:** Daily / weekly repeat program, Direct Record, Manual timer, Record Link, Turbo timer, VIDEO Plus+, VPS/PDC recording control

Accessories

- **Batteries:** 2 size AA
- **Cables:** Aerial cable
- **Remote control:** Zappa
- User manual

Dimensions

- **Product dimensions (W x H x D):** 435 x 93 x 226 mm
- **Product weight:** 2,6 kg

Power

- **Mains power:** AC 220 - 240 V +/- 10%

Product highlights

Digital Studio Picture Control

Smart Picture

Smart Picture provides the optimum picture settings for colour, brightness, saturation, contrast, sharpness, etc. to enhance your overall viewing experience at all times.

NTSC Playback

Turbo Drive

Follow TV

The video recorder or DVD recorder matches the stations and presets of your TV. Analogue: A signal comparison is made between TV and recorder via SCART cable. The user has to select every present available in his TV set. Digital: The re-sorting is done fully automatically.

VPS/PDC

With 'VPS' (Video Programming System) and 'PDC' (Program Delivery Control), the TV station controls the beginning and the length of the programmed recording. This means that your recording device switches itself on and off at the right time even if a TV program you have programmed begins earlier or finishes later than expected.

Automatic long play recording

Front A/V connectors

VIDEO Plus+

With the VIDEO Plus+ system, all you need to do to program your video recorder is to enter the 'Pluscode' – a single code of up to nine digits (but usually less) that is printed next to each TV program in most TV guides.

Turbo timer

Record Link

When you want to record a programme from your satellite receiver or any other external device just activate the "Record Link", put the set in standby and programme the desired timer on your satellite receiver. Upon activation of the satellite receiver, the set will start the recording simultaneously.

NICAM Digital Stereo

TV programs are broadcast with NICAM digital stereo sound. It offers CD-quality sound with a high immunity to noise and signal degradation. It can be used with mono, stereo and Dolby Pro Logic broadcasts. The integrated tuner of this product is fully equipped to decode the NICAM signal.



Date of issue 2006-07-07

Version: 4.0

12 NC: 8637 000 01169
EAN: 87 10895 80359 5

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.
© 2006 Koninklijke Philips Electronics N.V.
All Rights reserved.
www.philips.com