

Video Cassette Recorder

VRA671AT

Hi-Fi Four-Head Video Cassette Recorder with VCR Plus+™ Programming

- Four-head, double azimuth design
- Hi-fi stereo sound
- Remote Locator™
- ShowGuard™ Timer/programmer backup memory—indefinite!
- SmartClock™ with time zone select
- 19 Micron head
- “Commercial” skip search
- Auto DBS RecordLink™
- Front panel menu access
- Child lock
- Front panel audio/video inputs
- Clock/function display
- Variable slow motion



Full Auto-Feature Package

- Power On
- Digital Auto Tracking
- Auto Play
- Auto Repeat
- Auto Rewind
- Auto Eject
- Auto Power Off



As an ENERGY STAR® Partner, Philips has determined that this product meets the ENERGY STAR® guidelines for energy efficiency.



VCR/Universal TV/CBL/DBS Remote

Let's make things better.

PHILIPS **MAGNAVOX**

Programming & Playback Features

Hi-Fi Stereo Sound with Built-In MTS/SAP Decoder

Record stereo videotapes from stereo sound sources and playback pre-recorded hi-fi stereo tapes in hi-fi stereo sound—with an excellent 90dB+ dynamic range—through a stereo-equipped TV or regular TV and stereo hi-fi home audio system. The built-in MTS/SAP decoder allows reception and recording of off-air television stereo broadcasts and second audio program transmissions, where available. Back-up memory logic retains the cable channel guide map indefinitely even during a power failure or when the VCR is disconnected from its power source.

VCR Plus+™ Programming

Simplifies VCR programming by allowing you to simply enter PlusCode® programming numbers found in many published television listings. When recording begins, your VCR automatically selects the proper TV channel and program length. Back-up memory logic retains the cable channel guide map indefinitely even during a power failure or when the VCR is disconnected from its power source.

Auto DBS RecordLink™

One-Touch Record

8-Event/1-Year Smart Programming

Remote Control Onscreen Menu Programming

Picture

4-Head, Double Azimuth Design

Combines direct drive cylinder and capstan motors with precision digital servo control to produce excellent special effects reproduction—Still, Slow, and with the appropriate remote control, Frame Advance, Variable Slow Motion and x2 Play—in both SP and SLP speeds.

19 Micron Head

Digital Auto Tracking System

Auto Head Cleaner

Convenience

ShowGuard™ Timer/Programmer Backup Memory—Indefinite!

Now all your timer/programming is safe, regardless of power outages. Information is stored indefinitely in the system EEPROM.

SmartClock™

This menu-driven feature automatically maintains the correct time, regularly checking and updating the time if necessary. It also resets the clock after a power failure. The menu-driven time zone feature allows selection of appropriate time for those who live in a time zone other than that of their CATV service provider.

Front Panel Menu Access

Access most menu operations conveniently and quickly through the front panel of the VCR.

Child Lock

Front Panel Audio/Video Inputs

Daylight Savings Time Adjustment

Clock/Function Display

Bilingual (English/Spanish) Onscreen Function Display

Record End Search

Automatic Channel Setup

181-Channel FS Tuning

Onscreen Real-Time Counter with Time Search

Timer/Programmer Backup System

Repeat Play

Quick Start Mechanism

Audio/Video Input/Output Jacks

* ENERGY STAR is a U.S. registered trademark.

Auto DBS RecordLink, Remote Locator, ShowGuard, and SmartClock, are registered trademarks of Philips Consumer Electronics Company.

VCR Plus+ is a registered trademark of Gemstar Development Corporation.

The VCR Plus+ system is manufactured under license from Gemstar Development Corporation.

Special Effects

Variable Slow Motion

View SP or SLP video recordings in slow motion in both forward and reverse modes. Slow motion speed can be adjusted from 1/5th to 1/60th normal speed in either direction.

15x Forward/Reverse Latching Search

Search in forward or reverse mode at 15 times normal playing speed in SLP. The Latching Search feature provides continuous forward or reverse search with a single touch of the control. A second touch stops the search operation and returns the unit to the Play mode.

“Commercial” Skip Search

Frame Advance

x2 Play

Index Search System

Remote Control

Remote Locator™

Lost or misplaced remotes are easy to find! Simply press the Power button on the VCR. The words “Locating Remote” appear on the screen, and the remote control beeps—leading you right to it.

Backlit LED Remote Control

Makes it easy to use all remote VCR functions even in low light conditions. No more fumbling with tiny buttons, just press any opaque button on the transmitter and all major function buttons light up.

VCR/Universal TV/CBL/DBS Remote

Multifunction infrared remote controls all operating features and functions of this VCR, plus select functions of most Philips Magnavox and some competitive brand television sets, as well as some cable converter/decoders, and standard features of MAGNAVOX, RCA, and SONY digital broadcast satellite receivers. Change channels fast with the numeric direct access keypad and heads-up onscreen display for confirmation.

Full Auto-Feature Package

- Power On
- Digital Auto Tracking
- Auto Play
- Auto Repeat
- Auto Rewind
- Auto Eject
- Auto Power Off

UPC: 037849880234

Product Dimensions: 15.7"W x 3.6"H x 9"D

Product Weight: 7 lbs.

Carton Dimensions: 18.1"W x 6.6"H x 12.8"D

Carton Weight: 9 lbs.

Master Pack: 1

Contains: Four-Head, Hi-Fi Stereo Video Cassette Recorder, VCR/Universal TV/CBL/DBS Remote Control with Lighted Buttons and Batteries, RF Coaxial Cable, Operating Instructions, Warranty Information

INTERNET ADDRESS: <http://www.philipsusa.com>

Printed in U.S.A.

©1999 Philips Consumer Electronics Co.
A Division of Philips Electronics North America Corp.
Specifications subject to change without notice.

Subject to modification without notice.

Let's make things better.

PHILIPS MAGNAVOX