



High resolution sound, in the comfort of home

With the Fidelio X2HR headphones, you're in for an authentic listening experience in exquisite sound and comfort, in your very own home. Immerse in pristine sound details and custom-fit design that's crafted for your total enjoyment.

Full immersion in pristine details

- High Resolution audio reproduces music in its purest form
- Powerful 50mm neodymium drivers for wide yet precise range
- Acoustic open-back architecture for pristine audio fidelity
- Double-layered earshells engineered for sound precision
- Layered motion control diaphragm delivers precise sound
- Pre-tilted drivers fit the ears for minimal sound reflection

Crafted for comfort

- Breathable velour cushions to help dispel pressure and heat
- Deluxe memory foam earpads for long-wearing comfort
- Self-adjustable airy hammock with 3D mesh for a perfect fit


Intuitive and enjoyable ease of use

- 3.5mm to 6.3mm adaptor included
- Dedicated cable management clip for tangle-free ease


Philips Fidelio
Headphones

High resolution audio

Over-ear
Deluxe memory foam cushions



X2HR



PHILIPS
Fidelio

Headphones

High resolution audio Over-ear, Deluxe memory foam cushions

Highlights

50mm high power drivers



Each speaker is carefully handpicked, tuned and tested, and is being paired for the most detailed natural sound. The 50mm drivers utilize high power neodymium magnets to reproduce all your music's dynamics and deliver well balanced crisp bass, transparent mid-range and pristine high frequencies.

Acoustic open back design



An acoustic open-back architecture eliminates air pressure build-up behind the driver, allowing the diaphragm ample free movement, greatly enhancing sound transparency and smoothening extended high frequencies.


Layered motion control



Layered Motion Control (LMC) drivers feature a multi-layered polymer diaphragm that


encases a layer of damping gel. These layers form a flexible boundary and – together with the gel – absorbs and dampens any exaggerated frequencies, resulting in a smooth and flatter frequency response. The result is a more balanced, natural and refined range of high frequency sounds.

Self-adjustable hammock



The self-adjustable lightweight hammock features an airy 3D mesh, which is not only breathable, but is flexible enough to ensure a perfect fit – always.

Breathable velour cushions



Crafting the Philips Fidelio X2HR starts with meticulously choosing each material for its functionality and ergonomic comfort. Deluxe memory foam ear-pads are matched with a velour material of optimized density with high breathability, to dissipate pressure and heat for longer-wearing comfort.

Double layered earshells

The Philips Fidelio X2HR's double layered earshells are engineered to reduce resonance and vibration, bringing you flawless sound with genuine precision and uncompromised detail. The solid, layered construction ensures

X2HR/00

durability, making X2HR the ideal music companion at home.

Memory foam earpads

The materials used for the Fidelio X2HR are carefully selected to ensure long-wearing comfort and enhanced sound performance. Deluxe breathable ear pads with memory foam are designed for optimal ergonomic fit. Not only does the foam mold itself perfectly to the shape of your ear, it also seals in bass sounds while keeping out ambient noise.

High resolution audio



High Resolution Audio offers the best in audio performance, reproducing original studio master recordings more faithfully than 16bit/44.1kHz CD formats. This uncompromising quality makes High Resolution Audio the best sound companion for the music lover. Fidelio headphones meet the stringent standards required for the Hi-Res Audio stamp of quality. Whether enjoying your Hi-Res collection or a more traditional music source, the smooth extended high frequencies of the Fidelio headphone range help you get more from your music.

Headphones

High resolution audio Over-ear, Deluxe memory foam cushions

X2HR/00

Specifications

Sound

- Acoustic system: Open
- Diaphragm: LMC
- Frequency response: 5 - 40 000 Hz
- Impedance: 30 Ohm
- Magnet type: Neodymium
- Maximum power input: 500 mW
- Sensitivity: 100 dB @ 1mW
- Speaker diameter: 50 mm
- Distortion: <0.1% THD
- Type: dynamic

Connectivity

- Cable Connection: detachable Oxygen free cable (3m)

Accessories

- Adaptor plug: 3.5 - 6.3 mm adapter
- Cable management: Cable clip

Outer Carton

- Gross weight: 2.15 kg

- GTIN: 1 69 51613 99201 9
- Outer carton (L x W x H): 26.5 x 25.5 x 31 cm
- Nett weight: 0.87 kg
- Number of consumer packagings: 2
- Tare weight: 1.28 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 24 x 32 x 12 cm
- EAN: 69 51613 99201 2
- Gross weight: 0.91 kg
- Nett weight: 0.435 kg
- Number of products included: 1
- Packaging type: Carton
- Tare weight: 0.475 kg
- Type of shelf placement: Both

Product dimensions

- Product dimensions (W x H x D): 19 x 23 x 11 cm
- Weight: 0.38 kg



Issue date 2020-02-21

Version: 8.2.4

12 NC: 8670 001 41881
EAN: 69 51613 99201 2

© 2020 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com