

PHILIPS

Slim

Xperion 6000

500 lm Boost / 250 lm Eco

150 lm Spotlight

Battery life: 4.5 h (Eco: 7 h)

Versatile and rotatable



X60SLIMX1



Designed with you in mind

Advanced lighting performance that lasts

The Philips Xperion 6000 Slim is versatile and ideal for narrow spaces. Featuring 250 lm in Eco and 500 lm in Boost mode, the unique 270° rotating light module will help you direct the powerful beam where you need it.

See where others can't

- Premium LED light with multiple outputs
- Long running time in different light modes

Smart, ergonomic design

- Precision, 270° rotatable light
- Smart rotatable hook with magnet and ergonomic body

Handles tough conditions easily

- Resistant to impacts, water and solvents (IP54/IK07)

Extended warranty


- Extend your warranty online to 3 years

Accessories available to upgrade your work lamp

- Smart solutions for charging and finding your device

Highlights

Multiple light modes



Featuring high-quality and bright LED light, the Philips Xperion 6000 Slim displays objects faithfully and vibrantly via a high-luminosity, wide-beam main source producing 250 lm in Eco and 500 lm in Boost mode. Use the spotlight source with a 150 lm torch beam to see better and spot the smallest details.

Light modes for multiple needs



The Philips Xperion 6000 Slim is designed to be ready for action. A single charge provides enough energy for a full day's work: up to 7 hours in Eco mode, 4.5 hours in Boost mode and 9 hours with the torch beam. Powered by a powerful Li-ion battery, the Philips Xperion 6000 Slim can be fully charged within 4 hours via USB-C, ensuring maximum usage of its bright LED light.

Illuminate your work



The Philips Xperion 6000 Slim is a versatile lamp ideal for illuminating narrow spaces. Thanks to its unique 270° rotating light

module, you can easily position the light where you need it. There are multiple positions to help you work around small corners. This work light folds in half for compact storage.

Enables hands-free working



Designed with you in mind, the ergonomically shaped handle with an anti-slip coating allows you to hold this work light securely. If you need both hands free for work, position the light securely thanks to the 360° rotatable, retractable hook and a strong magnet. The power button is located on the back to ensure that the light does not glare directly at your eyes when you turn it on.

Designed for resistance



Designed to handle tough work environments with IK07 shock resistance, water-resistant to IP54 standards, and a surface to withstand chemicals and workshop solvents, the Philips Xperion 6000 Slim is built to last because we know that even the steadiest hands need the extra support.

Up to 3 years' warranty



Benefit from the Philips standard 2 year warranty plus 1 additional year¹

Upgrade your work light



Don't worry about losing your device any more. You can find it easily with the "Find My Device" function. Use the remote control to trigger an audible buzzer and flashing light to locate your device. The vibrant lime-green body will help you spot your device even in dark settings. To keep your work light to hand and ready to use, try the Philips Dock station. Placed on a table, it provides cordless charging for your lamp.² Find out more: [Philips.com/Xperion-6000](https://www.philips.com/Xperion-6000)

Specifications

Electrical characteristics

Battery capacity: 2600 mAh
Battery charging time: Up to 4 hours
Battery run time (boost): Up to 4.5 hours
Battery run time (eco): Up to 7 hours
Battery run time (pointer): Up to 9 hours
Battery type: Lithium battery
Charging cable type: Type C USB
Plug type: EU plug (not included for UK)
Voltage: 3.7 V
Wattage: 5 W
Power source: Rechargeable battery

Light characteristics

Beam angle: 100 degree
Beam angle (pointer): 15°
Colour temperature: 6000 K
Light output (boost): 500 lumens
Light output (eco): 250 lumens
Light output (pointer): 180 lumens

Marketing specifications

Expected benefits: Designed with you in mind
Product highlight: Versatile and rotatable

Ordering information

Order entry: X60SLIMX1
Ordering code: 01467231

Outer pack information

Height: 18 cm
Length: 19.5 cm
Width: 16.5 cm

Packaging Data

EAN1: 8719018014672
EAN3: 8719018014689

Packed product information

Cable length: 100 cm USB cable, 5 V 1 A adapter
Height: 17.5 cm

Length: 5.2 cm

Pack Quantity / MOQ: 6
Weight with batteries: 334 g

Product description

Hands-free options: Rotatable hook, strong magnet
Hook: 360° rotatable
Impact protection rating (IK): IK07
Ingress protection rating (IP): IP54
Magnet: 2 magnets
Materials and finishing: Robust ABS + Soft rubber
Operating Temperature: -10°C to 40°C
Resistant to: Grease, oil, workshop solvents
Technology: COB LED
UV leak detector: No
Range: Xperion 6000

