

PHILIPS

Stick vacuum
cleaner

SpeedPro Max

360° suction nozzle

25.2 V, up to 65 min runtime

2-in-1: vacuum & handheld



XC7041/01



The fastest cordless cleaning experience* with 360° suction nozzle

The revolutionary SpeedPro Max with 360° suction nozzle picks up more dirt with every stroke, forward and back – even along walls and furniture. Clean more in less time on both hard floors and carpets.

Unrivalled speed

- 360° suction nozzle captures dust and dirt from all sides
- LED nozzle reveals hidden dust and dirt

Unmatched airflow

- PowerCyclone 8 – our most powerful bagless technology
- PowerBlade digital motor creates high airflow (>1000 L/min)
- The Triple filtration system ensures high airflow for longer

Uninterrupted cleaning

- Up to 65 minutes of cleaning power with 25V Li-Ion batteries
- Integrated handheld unit, crevice tool and brush
- Fast reach everywhere, even under low furniture
- Unique dust bucket design empties without dust clouds
- Smart digital display indicates speed and battery usage

Highlights

360° suction nozzle



360° suction nozzle captures dust and dirt faster with every stroke, even backwards and against edges, to make every move count.

PowerBlade digital motor



PowerBlade is a digital motor engineered for unmatched, high airflow (>1000 L/min) that produces 360° suction at the nozzle. Register at Philips.com within 3 months of purchase and enjoy a free 5-year motor warranty!

PowerCyclone 8 technology



PowerCyclone 8 technology - our best bagless vacuum cleaning technology now in a cordless stick, to keep stronger suction for longer.

Up to 65 minutes runtime



High performance 25.2 V lithium ion batteries provide up to 65 minutes Eco runtime, 30 min in normal mode and 21 min in Turbo mode before you recharge.

Triple filtration system




The triple filter system returns only the clean air back to the motor, ensuring high airflow for longer

Smart power control



Smart digital display indicates speed and battery usage, and lets you know when it's time to clean the filter.

LED nozzle



Dust, fluff, hair and crumbs are easy to spot and eliminated with LED lights in the SpeedPro Max nozzle. LED nozzle reveals even the hidden dirt.

Fast reach everywhere



SpeedPro Max is flexible and easy to maneuver. The dust bucket is on top, which allows for a lower angle and even goes fully flat on the floor to reach under low furniture.

Hygienic emptying



The vacuum cleaner's dust bucket is easily removed and emptied hygienically without causing any dust cloud.

Specifications

Performance

Battery type: Li-Ion
Battery voltage: 25.2 V
Charging time: 5 hour(s)
Runtime: 65 minute(s)
Runtime (turbo): 21 minute(s)
Sound power level: 84 dB
Airflow (max): >1000 l/min

Filtration

Dust capacity: 0.6 L
Motor filter: Washable filter

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Design

Color: Beluga Silver

Nozzles and accessories

Accessories included: AC power adaptor,
Integrated brush, Wall-mount docking
Standard nozzle: 360° suction nozzle

Weight and dimensions

Weight of product: 2.73 kg

