

# PHILIPS

Bagged vacuum cleaner

3000 Series

99.9% dust pick-up \*

900W

Allergy filter

XD3112/09



## Captures and locks 99.9%\* of dust and allergens in a compact and lightweight design

With the new Philips Performer Compact vacuum cleaner, compact design meets king-size performance. Enjoy thorough cleaning throughout your home thanks to AirflowMax technology and our TriActive nozzle which features 3 cleaning actions in 1.

### Superior performance


- Revolutionary AirflowMax technology for strong suction power
- 900W motor for high suction power
- 99.9% dust pick-up\* to deliver thorough cleaning results
- Allergy H13 filter system captures >99.9% of fine dust
- Certified allergy friendly by ECARF.
- TriActive nozzle for 3-way thorough cleaning action

### Effortless cleaning

- Compact and lightweight for easy carrying
- Long 9-meter reach goes further without unplugging
- Soft brush integrated into handle, always ready to use


# Highlights

## AirflowMax technology



Uniquely designed dust chamber maximizes capacity and airflow with a non-clogging dustbag, that enables strong suction power right up until the dustbag is full.

## High-efficiency 900W motor



High-efficiency 900W motor delivers high suction power for thorough cleaning results.

## 99.9% dust pick-up\*



TriActive nozzle and high suction power ensure you can vacuum 99.9% of fine dust\*.

## Compact and lightweight




Compact and lightweight design ensure both storing and carrying the vacuum is easy.

## Long 9-meter reach



9-meter reach from plug to nozzle allows longer use without unplugging.

## Allergy H13 filter



Allergy H13 filter system catches >99.9% of fine dust particles - including pollen, pet hair and dustmites - ideal for allergy sufferers. Filtration level is equivalent to HEPA 13\*\*.

## ECARF certified



Certified allergy friendly by ECARF.

## Integrated brush



Dusting brush tool is built into the handle so it's always ready to use on furniture, flat surfaces and upholstery.

## TriActive nozzle



TriActive nozzle utilizes 3 cleaning actions in one go. The specially designed soleplate removes dust from deep within carpets, while the large front opening sucks up big bits. Air channels on both sides of the nozzle pick up any dust and dirt alongside walls or furniture.

# Specifications

## Performance

Input power (IEC): 899 W  
Input power (max): 900 W  
Sound power level: 79 dB  
Vacuum (max): 22 kPa

## Design

Color: Deep Black

## Filtration

Dust bag type: s-bag Classic Long Performance  
Dust capacity: 3 L  
Exhaust filter: Allergy filter  
Motor filter: 1 layer foam filter

## Usability

Action radius: 9 m  
Carrying handle: Front  
Cord length: 6 m  
Tube coupling: ActiveLock  
Tube type: Metal 2-piece telescopic tube  
Wheel type: Rubber

## Nozzles and accessories

Accessories included: Crevice tool, Integrated brush  
Standard nozzle: TriActive nozzle

## Sustainability

Packaging: > 90% recycled materials  
User manual: 100% recycled paper

## Weight and dimensions

Dimensions of product (LxWxH): 400 x 282 x 251 mm  
Weight of product: 4.6 kg

