

Philips  
Xenon HID conversion kit

Conv. electronics  
85V  
35W

XLDCKG4X2



## Easy fit for better sight

The Philips Xenon HID conversion kit is your chance to convert from standard halogen headlamps to the brightest and whitest Xenon bulbs.

### **Xenon HID Bulb - Genuine Philips quality**

- Original HID bulbs
- Superior beam pattern
- Comprehensive product available for almost all car models

### **Ballast - Easy Installation**

- Intergrated ballast with starter

# PHILIPS

Xenon HID conversion kit  
Conv. electronics 85V, 35W

# Specifications

## Technical specifications

- Base: G4
- Description: Conv. Electronics
- Range: G4

- Voltage: 85 V
- Wattage: 35 W

## Packaging Data

- Packing: X2

**XLDCKG4X2**

# Highlights

## Original HID bulbs

Original HID bulbs

## Superior beam pattern

3-axis alignment

## Comprehensive product

Comprehensive product available for almost all car models

## Integrated ballast

Integrated ballast with starter



Issue date 2016-12-21

Version: 2.0.1

12 NC: 8670 001 01432

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)